



ROEBUCK ADJUSTABLE WRENCH 24" PHOSPHATE

Manufactured from chrome vanadium steel these wrenches exceed the requirements specified by BS6333-83, US Fed

GGGW-631B and DIN standards

Thinner jaws and non-protruding shank allow working in confined spaces

Ergonomic handle provides comfort in use and efficient working grip

Measurement scale gives approximate size of nuts, pipes, etc

Associated Products	046527
Capacity, jaw Imperial	2-7/16
Capacity, jaw max	62 mm
Length	600 mm
Length, Inches	24 "
RoHS Compliant	NA