

H0,5/14 ZH OR SV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- in multipack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code

General ordering data

Order No.	9004440000
Type	H0,5/14 ZH OR SV
Version	Wire end ferrule, 0.5 mm ² , 8 mm, Colour code: Weidmüller, Orange
GTIN (EAN)	4008190198473
Qty.	500 pc(s).

H0,5/14 ZH OR SV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	14 mm	Net weight	0.124 g
--------	-------	------------	---------

Product data

Conductor cross-section	0.5 mm ²	Wire connection cross section AWG, max.	AWG 20
Contact surface length (L2)	8 mm	Collar height (A)	5 mm
Collar width (B)	3 mm	Contact surface diameter (D1)	1.4 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.3 mm

Classifications

ETIM 2.0	EC000005	ETIM 3.0	EC000005
UNSPSC	31-16-31-02	eClass 4.1	27-06-07-01
eClass 5.1	27-40-02-01	eClass 6.0	27-40-02-01
eClass 7.0	27-40-02-01		

Product information

Description of article	Twin wire end ferrule, orange
------------------------	-------------------------------

Approvals

Approvals

