

IP30 Lighting Connectors

3, 4 & 5 Pole options available

Part Number	Description
HYGST-30PSK	3-pole black male + female parts+ protection covers without locking latch
HYGST-3LPSK	3-pole black male + female parts+ protection covers with locking latch
HYGST-4LPSK	4-pole black male + female parts+ protection covers without locking latch
HYGST-5LPSK	5-pole black male + female parts+ protection covers with locking latch

Specification:-


Housing: Polyamide 66 (94-V2 grade)
 Metal Part: Plated Brass/Stainless Steel

Voltage / Ampere : 250V/16A

Ambient Temperature : T110°C


Wiring Capacity : 0.5 - 2.5mm²

- Compliant with EN 61984 (VDE0627)
- Designed for use with 3-core Round Cable.
- Plug/Skt connection Keyway protected to avoid incorrect assembly
- Touch-proof/Safe when disconnected under load
- Compatible with most other major EU lighting connectors of similar style.



Tel :-
01933 234400

Fax :-
01933 234411



Web :- www.hylec-apl.com

Email :- sales@hylec-apl.com

Making The Right Connections