

Plug and Socket Terminal Blocks


Specification:-
 Housing: Polyamide 6/6
 Insert : Brass, nickel plated
 Screw : Plated-steel
 Spring : Stainless Steel

Features & Benefits:-
 High Foot meets lighting application requirements & allows moisture run-off when used in enclosure.
 Solid brass pin for better conductivity.
 Stainless steel spring has better memory than split pin allowing greater number of insertions.
 UL & VDE approval


Hylec-APL Part Number	HYPS-01712	HYPS-02412	
	<u>T06</u>	<u>T10</u>	
Voltage (V)	250*	250*	* For UL-standard, max 300V
Ampere (A) VDE / IEC-rated	6	10	
Max Wiring Capacity (mm ²)	2.5	4.0	

Ambient Temperature : T105°C

Dimensions (mm)	<u>T06</u>	<u>T10</u>
Height	17	24
Length	115	140
Width	23	24
Spacing	9.6	12



Tel :-
01933 234400
Fax :-
01933 234411



Web :- www.hylec-apl.com

Email :- sales@hylec-apl.com

Making The Right Connections