


flat cable clamp - flat cables up to 64-conductor widths

WITH SPLIT END CAPS, HARDWARE MOUNT. Ferrite assembly press-fitted into a pair of nylon end caps. Mounts using screws, push-rivets, or other hardware. Ten sizes accommodate flat cables up to 64-conductor width.



PART No.	A	B	C	D	E	F	G	IMPEDANCE IN OHMS							
SE28B0071	.375	9,5	.815	20,7	1.190	30,2	.060	1,5	.470	11,9	.510	13,0	.900	22,9	49 @ 100MHz
SE28B0121	.375	9,5	1.315	33,4	1.190	30,2	.060	1,5	1.000	25,4	1.000	25,7	.900	22,9	97 @ 100MHz
SE28B0146	.375	9,5	1.565	39,8	1.190	30,2	.060	1,5	1.250	31,8	1.260	32,0	.900	22,9	120 @ 100MHz
SE28B0221	.375	9,5	2.315	58,8	1.190	30,2	.060	1,5	2.000	50,8	2.010	51,1	.900	22,9	176 @ 100MHz
SE28B1240	.625	15,9	1.365	34,7	1.829	46,5	.040	1,0	.725	18,4	1.020	25,9	1.500	38,1	250 @ 100MHz
SE28B1729	.625	15,9	1.849	47,0	1.829	46,5	.060	1,5	1.300	33,0	1.355	34,4	1.500	38,1	200 @ 100MHz
SE28B2480	.625	15,9	2.570	65,3	1.829	46,5	.060	1,5	2.000	50,8	2.047	52,0	1.500	38,1	250 @ 100MHz
SE28B3012	.625	15,9	3.125	79,4	1.829	46,5	.060	1,5	2.550	64,8	2.540	64,5	1.500	38,1	286 @ 100MHz
SE28B3500	.625	15,9	3.620	91,9	1.829	46,5	.060	1,5	3.020	76,7	3.000	76,2	1.500	38,1	290 @ 100MHz
SE28B4340	.625	15,9	4.460	113,3	1.829	46,5	.104	2,6	3.875	98,4	3.240	82,3	1.500	38,1	325 @ 100MHz

performance by part number:

