

- Replacement for incandescent 25 W
- Up to 85% energy saving
- Lifetime of 30,000 hrs
- An energy efficient LED solution for general lighting.



Order Code 52108

General Data

Lamp Socket E27
Design Frosted

Geometric Data

Length (mm) 112
Diameter (mm) 60
Weight (g) 155

Electric Data


Wattage (W) 4.5
Voltage (V) 220-240
Power Factor ≥ 0.40
Operating Frequency (Hz) 50-60

Photometric Data

Luminous Flux (lm) 280
CRI ≥ 80
CCT (K) 3000 – warm white
Luminous Intensity (cd) -
Beam Angle (°) -
Lifetime (hrs) 30,000

Switching Cycle 20,000

Wattage Equivalent (W) 25





Order Code	52108
Product Description	LED CLASSIC A E27 4.5W 3000K WW 280LM Blister

Technical Packaging Details

Barcode	023942521082
EAN 128	(02)00023942521082(37)04(91)204
EAN 14	50023942521087
Pack Dimensions (HxWxL)	198 mm x 118 mm x 61 mm
Pack Weight	156 g
Carton Qty (Shipping Unit)	4
Carton Dimensions (HxWxL)	208 mm x 135 mm x 248 mm
Cartons/Layer	24
Layers/Pallet	4
Units/Pallet	384

Photometric Diagram

52108

