

## Products

### 1 Port Fixed PowerCat FTP Shuttered Wallplate RJ45 568B - White



**Part No:** WNC-00010-02

**Region:** Western Europe, Eastern Europe

The PowerCat 5E Synergy Wall Plate range is ideal for space-limited areas such as power-poles, desktop trunking, or areas where a fixed number of ports are to be installed and modularity is not required. The product fits a standard UK back box (86 x 86mm outer dimension) and is a complete assembly unit. It includes the C5E RJLP connector, offering a low profile, space saving design that enables installation in shallow backboxes and trunking.

#### Features & Benefits

- UK Standard 86 x 86mm fascia
- Protected labelling facility and service I.D. icons
- Ideal for space-limited areas

#### Technical Info

##### Mechanical Characteristics

##### IDC Terminations

Suitable for 0.4mm - 0.6mm solid or stranded cable, maximum o.d 1.5mm

Two wires may be terminated for daisy-chain applications.

Patents pending on connector and module designs.

##### Mechanical

##### Jack Connector

Operating Life : Minimum 500 insertion cycles

Contact Material : Phosphor Bronze

Contact Plating : 1.25 micrometres Au/Ni

Material : UL 94VO Thermoplastic

##### IDC Connector

Operating Life: Minimum 100 Reterminations

Contact Material: Phosphor Bronze

Contact Plating: Sn/Pb over Ni

Wire Accommodation: 2 x 22-26 AWG solid or stranded

##### Optical/Electrical Characteristics

D.C. Resistance : <20mΩ

**Attenuation (dB)**

@ 1MHz 0.0121  
@ 16MHz 0.0193  
@ 100MHz 0.1052

**Crosstalk (dB)**

@ 1MHz -84.26  
@ 16MHz -60.03  
@ 100MHz -45.70

**PowerSum Worst Pair**

@ 100MHz-41.83

**Return Loss (dB)**

@ 1MHz -65  
@ 16MHz -48  
@ 100MHz -30

**Performance****Ordering Info**