

## MECHANICAL DETAILS

**Shell Style Model** FG\* : Straight plug cable collet and nut for fitting a bend relief


**Keying** 1 key (alpha=0, plug: male contacts, receptacle: female contacts)

**Housing Material** Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces

**Cable Fixing** 5.1 - 5.5 mm

**Variant 2** Z : Nut for fitting a bend relief

	A	L	M	S2
Mm.	13	42	28	9
In.	0.51	1.65	1.10	0.35



## PERFORMANCE DETAIL

**Insert** 1K.306 : 6 Low Voltage

**Insulator** L: PEEK

### Specifications

**Contact Type:** Solder

**Max. Matings:** 5000


**Contact Dia.:** 0.7 mm (0.028in)

**Bucket Dia.:** 0.8 mm (0.031in)

**Max. Stranded** 0.34 mm<sup>2</sup> (AWG 22)

**Max. Conductor:** 0.34 mm<sup>2</sup> (AWG 22)

**R (max):** 6.1 mOhm



## OTHER CHARACTERISTICS

**Shell Style/Model** Libellé

**Humidity (max):** <=95% [at 60 deg C /140 F]

**Vibration:** 15 g [10 Hz - 2000 Hz]

**Shock Resistance:** 100 g [ 6 ms]

**Salt Spray** >144 hr

**Climatical** 50/175/21


**Shielding (min):** 95 dB (10 MHz)

**Shielding (min):** 80 dB (1 GHz)







**IP Rating** 68



## Available Download

 [unipole\\_multipole.pdf](#)

## Related links

-  [Contact](#)
-  [Quote Request](#)
-  [Catalogs Downloads](#)
-  [Catalogs Requests](#)
-  [Sample Request](#)
-  [3D drawings](#)