




PHG.1K.306.CLLC55Z

MECHANICAL DETAILS


- Shell Style Model** PH* : Free receptacle cable collet and nut for fitting a bend relief
- Keying** 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
- Housing Material** Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces
- Cable Fixing** 5.1 - 5.5 mm
- Variant 2** Z : Nut for fitting a bend relief

	A	L	Sz
Mm.	15	45	9
In.	0.59	1.77	0.35




PERFORMANCE DETAIL

- Insert** 1K.306 : 6 Low Voltage
- Insulator** L: PEEK
- Specifications**
- Contact Type:** Solder
- Max. Matings:** 5000
- Contact Dia.:** 0.7 mm (0.028in)
- Bucket Dia.:** 0.8 mm (0.031in)
- Max. Solid** 0.34 mm² (AWG 22)
- Max. Stranded** 0.34 mm² (AWG 22)
- R (max):** 6.1 mOhm



OTHER CHARACTERISTICS

- Shell Style/Model** Libellé
- Humidity (max):** <=95% [at 60 deg C /140 F]
- Vibration:** 15 g [10 Hz - 2000 Hz]
- Shock Resistance:** 100 g [6 ms]
- Salt Spray** >144 hr
- Climatical** 50/175/21
- Shielding (min):** 95 dB (10 MHz)
- Shielding (min):** 80 dB (1 GHz)
- IP Rating** 68



Available Download

[unipole_multipole.pdf](#)

Related links

- [Contact](#)
- [Quote Request](#)
- [Catalogs Downloads](#)
- [Catalogs Requests](#)
- [Sample Request](#)
- [3D drawings](#)