

## MECHANICAL DETAILS

**Shell Style Model** PR\* : Free receptacle with cable collet


**Keying** 1 key (alpha=0; Plug: male contact; Receptacle: female contact)

**Housing Material** PSU (Polysulfone), gray

**Cable Fixing** 2.7 - 3.9 mm

**Variant 2** G : Gray collet nut

	A	L
Mm.	14	40
In.	0.55	1.57




## PERFORMANCE DETAIL

**Insert** 1P.M02 : 2 Low Voltage

**Insulator**

**Insulator**



## OTHER CHARACTERISTICS

**Shell Style/Model** Libellé

**F ret (min):** 50 N

**F ret (max):** 150 N







**IP Rating** 50



## Available Download

 [P\\_series\\_catalog.pdf](#)

## Related links

-  [Contact](#)
-  [Quote Request](#)
-  [Catalogs Downloads](#)
-  [Catalogs Requests](#)
-  [Sample Request](#)
-  [3D drawings](#)