

**UL MNX UL PC 125/75 HG**



Sample photo

**Order symbol:** UL PC 125/75 HG  
**Product nbr:** 6411308  
**Description:** UL Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074014337  
**El. number:**  
Finland:  
Denmark: 8212030284  
Italy: 7351057U  
Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		130	130	75	Ingress Protection (EN 60529): IP 66/67
<b>inch:</b>		5.1	5.1	3.0	Impact Resistance (EN 62262): IK 08
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>		Polycarbonate		Halogen free (DIN/VDE 0472, Part 815): Yes	
<b>Base colour:</b>		RAL 7035		UV resistance: UL 508	
<b>Cover colour:</b>		RAL 7035		Flammability Rating (UL 746 C 5): UL 746C 5V	
<b>Cover screws material:</b>		Polyamide		Glow Wire Test (IEC 695-2-1) °C: 960	
<b>Cover screws colour:</b>		Grey		UL Type: UL TYPE 1, 4, 4X, 6	
<b>Gasket material:</b>		TPE			
<b>Temperatures:</b>					<b>Certificates:</b>
<b>Short term:</b>		-40 ... 120 °C		Germanischer Lloyd (GL)	
<b>Continuous:</b>		-40 ... 80 °C		Underwriters Laboratories	
<b>Short term:</b>		-40 ... 250 °F		Det Norske Veritas	
<b>Continuous:</b>		-40 ... 175 °F		Fimko	
<b>Accessories:</b>					Europe EN 62208: 2003
					UL Canada
					Gost R

