

Compact small area floor cleaner

Standard accessories:

- Roller brush
- 2-tank system
- Mains operation
- Transport wheels
- 2 straight squeegees

Order no.: 1.783-207.0**Technical data**

Working width, brush (mm)	300
Working width, vacuum (mm)	300
Motor rating (W)	820
Battery Capacity	-
Battery Voltage	-
Tank fresh/dirt water (l)	4/4
Brush contact pressure g/cm ²	100
Brush rotation speed rpm	1450
Max. area performance (m ² /h)	200
Frequency (Hz)	50-60
Voltage V	230
Weight (kg)	12
Dimensions (L x W x H) (mm)	390x335x1180

Details

Description

The BR 30/4 C scrubber drier eliminates the hassle and safety risks associated with floor mopping in public areas. As easy to use as an upright vacuum cleaner, the BR 30/4 thoroughly cleans and dries floors in a single pass, and can also be used for deep cleaning. Using a BR 30/4 C is faster, easier, more hygienic and safer for operators and public than mopping, leaving floors instantly clean, safe and usable. The BR 30/4 C is designed to be safe and hygienic for operators. Its four litre clean and dirty water tanks are fully removable and easy to clean and refill, while the roller brush and squeegees can be removed and replaced without tools. The machine's exceptionally low cleaning head height (only 7cm) makes cleaning under furniture easy, while the vacuum can be switched off to enable initial scrub and detergent lay for deeper cleaning.

Features & Benefits

High-speed roller brush

Roller assists forward movement for easy cleaning.

The roller brush also cleans structured surfaces and joints.

Ten times higher contact pressure than manual cleaning.

Immediately dry

For intensive cleaning, the suction can be switched off via the foot pedal.

Floors dry very quickly.

The soft rubber squeegees remove moisture - backwards and forwards.

Vacuum off facility

Detergent can be applied and then vacuumed for deeper cleaning.

Vacuum can be switched off by foot pedal.

Tanks are removable

Tanks can be removed separately or together. Including handle for easy transport.

The dirty water tank can be removed separately and emptied into a sink, for example.

The handy fresh water tank can be removed and filled in small sinks.

Accessories

Microfibre shaft

Microfibre roller

World first: Microfibre roller, length 300 mm. Combines the excellent cleaning power of microfibres with the advantages of roller technology. Ideal for cleaning fine stoneware tiles.

Order no. 4.762-453.0



Miscellaneous

Filling hose

Order no. 6.680-124.0



Pump spray bottle 1 l

Order no. 6.394-409.0



Cleaning agent dosage kit, wall mounted DS 3

Directly connectable with the tab, water and detergent will be filled in the fresh water tank in the preset mixture. Can also be used with filling system kit.

Order no. 2.641-811.0



Extension cable

Extension cable, 20 m, 3x1.5 mm². With splash-proof earthing pin plug, strain relief and anti-kink sleeve.

Order no. 6.647-022.0



Roller brushes for BR

Roller brush, medium

Roller brush, medium-hard, red. Length: 300 mm. With wear-resistant star-wheel mechanism. For normal use. Bristles: Polypropylene, 0.2 mm thick, 11.5 mm long.

Order no. 4.762-428.0



Roller brush, soft

Roller brush, soft, white. Length: 300 mm. With wear-resistant star-wheel mechanism. For cleaning sensitive floors and polishing. Bristles: Polyamide, 0.15 mm thick, 11.5 mm long.

Order no. 4.762-452.0



Roller brushes for BR

Roller brush, carpet, soft, 300 mm

For carpet cleaning.

Order no. 4.762-499.0



Roller brush, high-low

Medium hard, for cleaning strong structured floors and deeper joints.

Order no. 4.762-484.0



Suction bar, complete

Suction bar complete Helima

Order no. 4.777-420.0



Squeegee, oil-resistant

Straight squeegee, oil-resistant, 300 mm. For cleaning, kitchens, workshops, restaurants, petrol filling stations, etc.

Order no. 4.777-324.0



Teppich Kits

Carpet cleaning kit BR 30/4 C

Order no. 2.783-005.0

