

Dry vacuum cleaners



# T 10/1 Professional

High value tub vacuum cleaner designed for professional cleaners

## Standard accessories:

- Suction hose 2.5 m
- Metal suction tube
- 2 x 0.5 m
- Filter bag Fleece
- Switchable floor nozzle 262 mm
- Antistatic system
- Container material Plastic
- Floor tool

Order no.: 1.527-411.0



## Technical data

|                             |             |
|-----------------------------|-------------|
| Air flow rate (l/s)         | 61          |
| Vacuum (mbar/kPa)           | 244/24.4    |
| Container capacity (l)      | 10          |
| Max. intake performance (W) | 1250        |
| Standard nominal size (mm)  | 32          |
| Length of cord access. (m)  | 12          |
| Sound level (dB(A))         | 63          |
| Weight (kg)                 | 6.5         |
| Dimensions (L x W x H) (mm) | 355x310x410 |

## Details

### Description

The T 10/1 Professional brings new levels of quality and value to the contract cleaner tub vacuum sector. With key features designed to keep purchase and maintenance costs low, the T 10/1 Professional offers the toughness, simplicity, performance and value contract cleaners demand.

---

### Features & Benefits

Large, round permanent main filter of washable nylon

Extremely strong and dense enough for vacuuming without a filter bag.

Service-friendly

The cord can be replaced quickly and easily by loosening two screws.

---

## Accessories

### Adapter (tube -> nozzle)

#### Adapter

From DN 32 to DN 35: Plastic adapter (electrically non-conductive). Suitable for BV and T vacuum cleaners.



Order no. 6.902-083.0

### All-purpose brushes

#### All-purpose brush, DN 32

All-purpose plastic brush Bristles: 120 x 45 mm. For all T and BV types.



Order no. 6.906-122.0

### Combi-nozzles (dry)

#### Combination floor tool (dry)

Plastic combination floor tool with changeover function (ID 32; 260 mm), with stainless steel base plate.



Order no. 6.906-211.0

#### Combination floor tool for parquet

Plastic combination floor tool for parquet (DN 32) with brush strips and two rollers, suitable for all industrial T vacuum cleaners. Combination floor tool without changeover function. 360 mm



Order no. 6.906-107.0

#### Combination floor tool

Plastic combination floor tool (dry) with stainless steel base plate and rollers. With changeover function.



Order no. 6.906-696.0

#### Combination floor tool

Plastic combination floor tool with plastic base plate and two rollers.



Order no. 6.906-812.0

#### Combi-nozzle (dry)

Plastic combination floor tool with changeover function (ID 32; 320 mm), with two small wheels.



Order no. 6.906-212.0

### Connecting sleeves

#### Adapter, DN 32/35, with internal thread

Electrically non-conductive adapter with internal thread. For connecting two suction hoses without connectors. Suitable for DN 32 or DN 35.



Order no. 6.902-077.0

### Crevice nozzles

#### Crevice nozzle

Plastic crevice tool (DN 32) for industrial dry vacuum cleaners for vacuuming in crevices and corners.



Order no. 6.903-403.0

## Exhaust air filter

### Motor protection filter felt

Order no. 6.414-611.0



## Extension hoses (Clip-system)

### Extension hose, C 32, C 35 clip system

Electrically non-conductive standard extension hose for all C-32 and C-35 hoses with clip system.

Order no. 6.906-237.0



### Extension hose C 32-, C 35-Clip-system, el.

for all C-32 and C-35 hoses, electrically conductive.

Order no. 6.906-277.0



## Fabric filter bag

### Fabric filter bag

Cotton filter bags, washable up to 40°C, suitable for T7/1, T 10/1 and T 12/1 models.

Order no. 6.904-316.0



## Fleece filter bags (3 ply)

### Fleece filter bags

Extremely tear-resistant, 3-ply fleece filter bags, dust class M. Fleece filter bags have 2 to 3 times the capacity of conventional paper filter bags. Standard for T 10/1 and T 12/1.

Order no. 6.904-315.0



### Fleece filter bags

Fleece filter bag, 3-ply, tear-proof, dust class M, large-scale consumer unit.

Order no. 6.904-321.0



## HEPA filter for dust class H

### ABS HEPA-filter T 191 and T 10/1

HEPA-filter cartridge with montage set for 6.414-634.0

Order no. 2.641-229.0



### HEPA filter cartridge

HEPA filter cartridge, paper / metal (H 13)

Order no. 6.414-634.0



## Main filter baskets

### Main filter basket with reinforced fleece

Plastic frames with reinforced fleece material, washably to 40°C.

Order no. 5.731-649.0



## Nozzle sets

### Nozzle kit ID 32, for T vacuum cleaners with clip holder

Nozzle kit (DN 32) for all industrial dry vacuum cleaners, includes crevice tool, upholstery tool, round brush and clip holder.

Order no. 2.860-143.0



## Paper filter (2 ply)

### Paper filter bags for T 7/1, T 10/1, x10

10 paper filter bags (BIA-C dust class M), suitable for all industrial dry vacuum cleaners (e.g. T 7/1 und T 10/1).

Order no. 6.904-333.0



### Paper filter bags, bulk consumer pack

For bulk consumers: 300 paper filter bags (BIA-C dust class M) suitable for all T 7/1 and T 10/1 industrial dry vacuum cleaners.

Order no. 6.904-337.0



## Plastic bend

### Plastic bend, C-ID 32

Plastic with C-32 clip system.

Order no. 4.408-051.0



### Comfort plastic bend, C-ID 32

Plastic bend (DN 32) with C-32 clip system with opening for adjusting the floor tool for high-pile or extremely dense textile coverings.

Order no. 4.440-865.0



### Plastic bend

Electrically conductive plastic bend (DN 32) with C-32 clip system, reduces static buildup. Optional for BV 111, T 7/1, T 191, T 10/1, T 12/1, T 201/T201 + ESB 28.

Order no. 4.408-052.0



## Radiator brushes

### Radiator brush

Radiator brush is suitable for crevice tool 6.903-403.0

Order no. 6.903-404.0



## Repair kits

### Repair set, C 32

Repair set (C32) includes threaded hose adapters for industrial T vacuum cleaners with clip system.



Order no. 2.639-739.0

## Suction brushes

### Suction brush

Rotatable suction brush (DN 32 plastic) with PA bristles, 70x45 mm. Only for BV and T vacuum cleaners.



Order no. 6.903-887.0

## Suction hoses (Clip-system)

### Suction hose, (clip system), C 32

2.5 m suction hose with dry vacuum cleaner connection, clip connection (C 32).



Order no. 4.440-911.0

## Suction hoses complete (Clip-system)

### Suction hose, complete (clip system), C DN 32, 2.5 m

Improved quality: 2.5 m suction hose with dry vacuum cleaner connection, clip connection and bend (C-DN 32).



Order no. 4.440-907.0

## Suction tubes metal

### Suction tube

Metal suction tube (DN 32, length 0.5 m) with black plastic coating, suitable as an extension, e.g. vacuuming ceilings.



Order no. 6.906-618.0

### Telescopic suction tube

Chromium-plated metal telescopic tube (DN 32, length: 0.61-1 m), suitable as an extension, e.g. vacuuming ceilings.




Order no. 6.903-524.0

### Suction tube

Metal

Order no. 6.903-850.0



## Suction tubes stainless steel

### Suction tube, DN 32

Stainless steel

Order no. 6.902-050.0



## Turbo nozzle

### Turbo nozzle

Plastic turbo upholstery nozzle (DN 35/32, 160 mm) with reduction sleeve.

Order no. 2.860-113.0



## Turbo nozzle

### Turbo nozzle, DN 32

Plastic turbo floor nozzle (DN 35/32, 270 mm) with reduction sleeve.

**Order no. 2.860-114.0**



## Upholstery nozzles

### Upholstery nozzle

Plastic upholstery tool (DN 32) with thread catcher, standard for T 201, T 201 + ESB 28. Optional for T 7/1, T 191, T 10/1.

**Order no. 6.903-402.0**

