
Item no.: 280-557
Product description: TRIPLE DECK TERMINAL BLOCK
GROUND/THROUGH/THROUGH



Produkt kann von Bild abweichen / product may differ

Packing unit 40 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Number of levels	3
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	20 A
Weight	21.769 g
Color	green-yellow/gray/gray
Wiring type	Front-entry
No. of connection Points	6
No. of potentials	3
Height	76.5 mm
Height	3.01 in
Width	5 mm
Width	0.197 in
Depth	103 mm

Depth	4.05 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
280-557	ABS	05-HG476175/3-PDA	500	20	2,5
280-557	BV	07436/Co	500	20	2,5
280-557	CCA	NL5855	500	20	2,5
280-557	CSA	154112-1536071	300	20	28-12
280-557	GL	17295-00HH	500	20	2,5
280-557	KEMA	2082859.07	500	20	2,5
280-557	LR	91/20112(E6)	500	20	2,5
280-557	PRS	TE/1718/880590/08	500	20	2,5
280-557	RMR	11130002	500	20	2,5
280-557	UR	E45172			28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected