


Item no.: 721-620
 Product description: MALE CONNECTOR 20 POLE PIN SPACING 5 MM / 0.197 IN
 100% PROTECTED AGAINST MISMATING WITHOUT
 PRECEDING GROUND CONTACT



Produkt kann von Bild abweichen / product may differ

Packing unit 10 pieces

RoHS compliant

Product group	3 (Multi Conn. System)
Weight	29.5 g
Color	light gray
No. of connection Points	20
No. of potentials	20
pole count	20
Height	14.3 mm
Height	0.563 in
Width	103.2 mm
Width	4.063 in
Depth	27.5 mm
Depth	1.083 in
Pin spacing from	5 mm
Pin spacing from	0.197 in
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	4 kV
Current intensity EN	12 A

Pollution degree	2
Measured voltage EN	630 V
Measured shock voltage	4 kV
Current intensity EN	12 A



Connection method	CAGE CLAMP® CONNECTION
Cross section [mm ²]	0.08 - 2.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [mm ²]	0.25 - 1.5 mm ²
Cross section [mm ²]	0.25 - 2.5 mm ²
Cross section [AWG]	28 - 12 AWG
Strip length from	8 mm
Strip length to	9 mm
Material group	I



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
721-620	ABS	04-HG469925/1-PDA	250	12	0,08-2,5
721-620	BV	11915/A0	250	12	
721-620	CCA	5764	250	12	0,08-2,5
721-620	CSA	154112-1466354	300	15	28-12
721-620	DNV	E-9218	250	12	0,08-2,5
721-620	GL	17296-00HH	250	12	
721-620	KEMA	2083746.02	250	12	0,08-2,5
721-620	KR	HMB05880-EL003	250/400	12/16	2,5
721-620	LR	96/20035	250	12	0,08-2,5
721-620	RMR	11130002	250	12	0,08-2,5
721-620	UR	E45171	600	20	12
721-620	UR	E45172	300	15	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected