


PRINT



Narrow-Tongue Copper Lug

T&B Catalog Number: 54152NT
UPC Number: 78620986791
Status: Active

Description:
Copper One-Hole Lug - Standard Barrel Narrow Tongue Lug - max 35KV, 1/0 AWG Wire, 1/4" Bolt Size, Tin Plated with Inspection Hole, Pink 42



INSTAL SUBMITTAL
PACKAGE

Where To Buy

Enter Zip Code:

Enter Quantity:

General

Material	Copper
Finish	Tin Plated
Wire Size	1/0 AWG
Number of Studs	1
Stud Size	1/4
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Tongue Width	Narrow
Peep Hole	Y
Marking	Standard
Hole Shape	Round
Die Color	Pink
Die Code	42

Dimension Information

A (inches)	1.600
B (inches)	0.650
C (inches)	0.521
D (inches)	0.125
E (inches)	0.521
F (inches)	0.250

Specifications

Voltage Rating	600V
----------------	------

Tooling

Connector & Tooling Chart [Click Here](#)

Packaging

Order Multiple	10
Inner Package	10
Outer Package	100
Package Height	3.43
Package Length	21.5
Package Width	8.5
T&B Sold in UOM	Each
T&B Weight Per UOM	5.5 lbs. per 100

Application Support

- T&B Sales Drawings [wsd-000288](#)
- T&B Instruction Sheets [ta00675-tb2](#)

Notes

- Dimensions given for reference only. Dimensions may vary up to +/- .030.

Certifications



File Nbr:
E9809

[Vertical Market Brochures](#)
[Where To Buy](#)

[Tool Services](#)
[Terms](#)

[News](#)