


PRINT



Where To Buy

Enter Zip Code:

Enter Quantity:

Splice Connector

T&B Catalog Number: RCC26
UPC Number: 78621081970
Status: Active

Description:
Insulated Nylon Parallel Splice Connector For Wire Range 14-12 Length .9 Diameter .28, Yellow

ROHS SUBMITTAL PACKAGE

Features

- Wires are laid side by side in the connector, and the splice connection is complete in one crimp.

General

Insulation Type	Insulated Nylon
Terminal Series	RCC
Material	Copper
Finish	Tin Plated
Color	Yellow
Wire Range	14-12

Dimension Information

Stock Thickness	.04
A (inches)	.90
B (inches)	.28

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

Tooling

Tool Charts	Click Here
Application Tools	WT2000, WT112M
Recommended Tool	ERG4001

Packaging

Order Multiple	500
Inner Package	500
Outer Package	5000
Package Type	Bulk
Package Height	7.7
Package Length	17
Package Width	10
T&B Sold in UOM	Each
T&B Weight Per UOM	0.3 lbs. per 100
Alternate Package Qty	2C12

Application Support

Overview	Click Here
Wire Guide Tables	Click Here

Certifications

RoHS Compliance Yes [Generate Compliance Certificate](#)

Certifications



File Nbr:
E9809

