



RBK HSS JOBBER DRILL 5/16"

DIN 338/BS 328

Flute Geometry Standard Helix, right hand spiral

Surface finish Blue

Point geometry Up to 2.9mm - 118° 3.0mm and above - 135° split point

Angle, drill point	118 °
Associated Products	023056
Diameter, drill bit Imperial	5/16 "
Diameter, External	5/16 "
Length, effective	75 mm
Length, overall	117 mm
Material	HSS
RoHS Compliant	NA