



## RBK HSS JOBBER DRILL 9.0MM

**DIN 338/BS 328**

**Flute Geometry** Standard Helix, right hand spiral

**Surface finish** Blue

**Point geometry** Up to 2.9mm - 118° 3.0mm and above - 135° split point

|                            |         |
|----------------------------|---------|
| <b>Angle, drill point</b>  | 118 °   |
| <b>Associated Products</b> | 023645  |
| <b>Diameter, External</b>  | 9.00 mm |
| <b>Length, effective</b>   | 81 mm   |
| <b>Length, overall</b>     | 125 mm  |
| <b>Material</b>            | HSS     |
| <b>RoHS Compliant</b>      | NA      |