


SACC-M 8MS-3QO-0,5-M

Order No.: 1441024

<http://eshop.phoenixcontact.net/phoenix/treeViewClick.do?UID=1441024>

Sensor/actuator connector, male connector, straight, 3-pos., M8, metal knurl, maximum cable diameter of 5.0 mm

Commercial data

EAN	 4 046356 515917
Pack	1 pcs.
Customs tariff	85366990
Gross weight in pieces	0.00784 KG
Net weight per piece (exclusive packing)	0.0077 KG
Catalog page information	Page 68 (PC-2011)

Product notesWEEE/RoHS-compliant since:
06/16/2009

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General data**

Rated current at 40°C	4 A
Rated voltage	60 V
Number of positions	3
Volume resistance	≤ 5 mΩ
Insulation resistance	≥ 100 MΩ

Ambient temperature (operation)	-25 °C ... 80 °C (Plug / socket)
General characteristics	
Standards/regulations	M8 plug-in connector IEC 61076-2-104
Coding	A - standard
Surge voltage category	II
Pollution degree	3
Degree of protection	IP65/67
Insertion/withdrawal cycles	≥ 100
Torque	0.6 Nm (Pressure nut) 0.2 Nm (M8 knurl)
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material of grip body	PA 6
Material, knurls	Nickel-plated brass
Connection method	Insulation displacement connection
Conductor cross section	0.25 mm ² ... 0.5 mm ²
AWG conductor cross section	24 ... 20
Wire diameter including insulation	0.75 mm ... 1.5 mm ±0.05 mm
Frequency of connections between conductors of the same cross section	10
External cable diameter	2.5 mm ... 5 mm ± 0.2 mm
Wire insulation material	PVC/PE/PP
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	Class 2-6
Status display	No
Stripping length of the sheath	40 mm

Certificates / Approvals



Certification

cULus Recognized, GOST

Certifications applied for:

Certification Ex:

Accessories


Item	Designation	Description
Cable/conductor		
1501689	SAC-3P-100,0-PUR/0,25	Cable ring, PUR halogen-free black, 3-pos., conductor colors: Brown/blue/black, cable length: 100 m
1501650	SAC-3P-100,0-PUR/0,34	Cable ring, PUR halogen-free black, 3-pos., conductor colors: Brown/blue/black, cable length: 100 m

Protection and sealing elements		
1430857	PROT-M 8 FS-PA-CHAIN	M8 sealing cap made of plastic with fixing band for sensor cables, for M8 plugs


Tools		
1208461	SAC BIT M8-D10	Nut for assembling sensor/actuator cables with M8 connector and for M8 connectors with QUICKON fast connection technology, for 4 mm hexagonal drive
1208487	TSD 02 SAC	Torque screwdriver, with preset torque of 0.2 Nm and 4 mm hexagonal drive for M8 connectors
1212224	TSD-M 1,2NM	Torque screw driver, accuracy as per EN ISO 6789 standard, adjustable from 0.3 - 1.2 Nm
1212600	TSD-M SAC-BIT ADAPTER	Adapter bit for TSD-M...torque tools, E6.3-1/4" drive with 4 mm hexagon to accommodate SAC bits

Diagrams/Drawings

Functional drawing




Dimensioned drawing



M8 x 1 male connector, straight version

Schematic diagram



Pin assignment M8 plug, 3-pos., view male side

Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford Shropshire TF7 4PG,GB
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



© 2013 Phoenix Contact
Technical modifications reserved;