



Datasheet for part number MDSM-15PE-Z10-VR22

Our Catalog Part Number: MDSM-15PE-Z10-VR22
Our Global Manufacturing Part Number: 121661-1042
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: MDSM

Product Datasheet	
Series	Micro MDSM
Mating Cycles	500
Layout	15 contacts
Gender	Pin
Termination Type	Solder pin 90°, spacing 1,27 x 2,54 mm, with rivet nut and grounding tab
Mounting Methode	Screw for wall thickness 1,5 mm
Packaging	22 pieces in tube packaging
Insulator	Thermoplast, UL94V-0
Contact guiding plate	PA, high temperature resistant
Shell	Steel, tinned and nickel plated
Contact Type	Copper alloy
Contact Finish	Gold over PdNi
Contact Termination Area	Tin
Wire size	AWG 26 - 28
Insulation diameter	0.95 mm max
Contact spacing	1.27 mm
Temperature range	-55°/+125°
Current rating	2.5 A / 25°C
Test voltage	350 Vrms
Contact resistance	35 mOhm max
Insulation resistance	500 mOhm min