



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: PV375

PowerVerter® 375W Ultra-Compact Inverter with 2 Outlets

Highlights

- 12V DC input; 120V AC output; 2 outlets
- 375 watts continuous output
- 600 watts peak output (instantaneous)
- Convenient cigarette lighter plug



Description

Utilize your vehicle's battery to efficiently power office equipment on the road. Continuously supplies up to 375 watts of 120V AC power to 2 AC outlets from any 12V battery or automotive DC source. Convenient cigarette lighter DC input jack with 3-ft. cable provides 1-step installation. Portable and compact, the inverter's design is among the most rugged available thanks to its lightweight metal casing.

Applications

- Ideal for laptop computers, portable electronics, battery chargers for cell phones, notepads, game systems, personal printers and battery rechargers for small battery-operated power tools, portable TV-VCR-stereo systems, camcorders, lighting and other low-power applications under 375 watts.

Package Includes

- PV375 Inverter
- Warranty information
- Instruction manual

Features

- Allows users to run AC devices from any 12V cigarette lighter socket
- Converts 12V DC battery power to 120V AC power
- 375 watts continuous output power; 600 watts peak output power (instantaneous)
- 2 outlets
- 3-ft. cord with cigarette lighter plug
- Ultra compact, lightweight design with all-metal housing
- Low battery alarm with auto-shutoff preserves vehicle battery
- Overload alarm with auto-shutoff prevents wattage overload
- Replaceable 40amp fuse protects inverter from overload
- Lighted power switch

Specifications

OVERVIEW	
Model Type	Inverters
OUTPUT	
Frequency compatibility	60 Hz
Output watts	375
Continuous output capacity (watts)	375
Peak output capacity (watts)	600
Output nominal voltage	120V
Output voltage regulation	Maintains PWM sine wave output voltage of 115 V AC (+/- 8 V AC)
Output frequency regulation	60 Hz (+/- 3 Hz)
Overload protection	40A automotive input fuse
Outlet quantity / type	2 AC outlets
INPUT	
Maximum input amps / watts	Full continuous load - 40A at 12V DC, No load - 0.65A at 12V DC
Input connection type	12V DC cigarette lighter input plug connection
Input cord length details	3 ft. hardwire input cable, 16 gauge, 2 wire
Voltage compatibility (VDC)	12
BATTERY	
DC system voltage (VDC)	12
LEDS ALARMS & SWITCHES	
Alarms	Dual function alarm indicates overload conditions or low DC input voltage of 10.5V or less.
Switches	Lighted on/off power switch
PHYSICAL	
Shipping weight (lbs)	2.5
Shipping weight (kg)	1.1
Cooling method	Fan
Unit Dimensions (HWD/in)	2 x 4.25 x 7
Unit Dimensions (HWD/cm)	5.08 x 10.8 x 17.78
Shipping Dimensions (HWD/in)	2.5 x 11.75 x 7.5
Shipping Dimensions (HWD/cm)	6.35 x 29.85 x 19.05
Unit weight (lbs)	2.3
Unit weight (kg)	1
Material of construction	Aluminum / sheet metal

Style	Compact
ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
SPECIAL FEATURES	
Appearance	Attractive, rugged, metallic blue color inverter system
Remote control capability	No
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2552.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.