

- Replacement for 15 W E14 candle lamp
- 80% energy saving
- Lifetime of 15,000 hrs
- Ideal for general and decorative lighting at home and in hospitality environments. This candle lamp enhances the appeal of the chandelier and other luminaires both when lit up and when not.



Order Code 52047

General Data

Lamp Socket E14

Design Clear

Geometric Data

Length (mm) 103

Diameter (mm) 35

Weight (g) 55

Electric Data

Wattage (W) 3.8

Voltage (V) 220-240

Power Factor ≥ 0.85

Operating Frequency (Hz) 50-60

Photometric Data

Luminous Flux (lm) 150

CRI ≥ 80

CCT (K) 2700 K – warm white


Luminous Intensity (cd) -

Beam Angle (°) -

Lifetime (hrs) 15,000

Switching cycle 100,000

Wattage Equivalent (W) 15





Order Code	52047
Product Description	LED Classic B 3.7W E14 2700K WW 150LM

Technical Packaging Details

Barcode	023942520474
EAN 128	(02)00023942520474(37)04(91)53
EAN 14	50023942520479
Pack Dimensions (HxWxL)	132 mm x 108 mm x 258 mm
Pack Weight	TBC
Carton Qty (Shipping Unit)	10
Carton Dimensions (HxWxL)	258 mm x 108 mm x 132 mm
Cartons/Pallet	42
Layers/Pallet	6
Units/Pallet	1680

Photometric Diagram

52047

