

**Passeinsatz für Einsätze E14 4 A
COMBI CHECK**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LED-Display
- acc. to VDE-Norm 0682, section 401
- high peak voltage strength
- the right tester for every application

General ordering data

Order No.	9918860000
Type	COMBI CHECK
Version	2-pole voltage tester, Yes
GTIN (EAN)	4032248405749
Qty.	1 pc(s).

Passeinsatz für Einsätze E14 4 A COMBI CHECK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Weight	290 g	Net weight	290 g
--------	-------	------------	-------

Product data

Rated voltage, min.	6 V	AC voltage measuring range	6-690 V
Frequency range, min.	0 Hz	Frequency range, max.	100 Hz
Rated voltage, max.	690 V AC/DC	Protection degree	IP 65
Battery type	1.5 V type AAA battery	Peak voltage resistance	8 kV
Display	LED	DC voltage display	6,12, 24, 50, 120, 230, 400, 690 V
AC voltage display	6,12, 24, 50, 120, 230, 400, 690 V		

Classifications

ETIM 2.0	EC000494	ETIM 3.0	EC000494
UNSPSC	41-11-36-37	eClass 4.1	27-20-03-08
eClass 5.1	27-20-03-08	eClass 6.0	27-20-03-08
eClass 7.0	27-20-03-08		

Product information

Description of article	Voltage tester up to 690 V/ 100 Hz LED
Product description	<ul style="list-style-type: none"> • Phase sequence indicator • Single-pole phase test • Batteries included

Approvals

Approvals



**Passeinsatz für Einsätze E14 4 A
COMBI CHECK**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

