



Glassfibre Exposed Welded Tip Thermocouples



Available in type K, J & T

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors.

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

- ◆ Thermocouple types K, J & T
- ◆ Fast response, welded exposed junction
- ◆ 1, 2 or 3 metre long glassfibre insulated flat pair cable
- ◆ Good temperature resistance (not suitable in fluids)
- ◆ 1/0.3mm conductors
- ◆ Temperature range -50°C to $+350^{\circ}\text{C}$ (short periods up to 400°C)
- ◆ Tolerance to IEC 584 Class 2
- ◆ Colour code to IEC 584-3
- ◆ Ideal for test & development applications

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com

<u>T/C Type</u>	<u>Length</u>	<u>+Positive tail wire</u>	<u>-Negative tail wire</u>	<u>Manufacturing Part Number</u>	<u>Farnell Order Code</u>
'K'	1 metres	Green	White	Z3-K-F/G-1/0.315-1.0-T	706-9224
'K'	2 metres	Green	White	Z3-K-F/G-1/0.315-2.0-T	707-6137
'K'	3 metres	Green	White	Z3-K-F/G-1/0.315-3.0-T	163-3479
'J'	2 metres	Black	White	Z3-J-F/G-1/0.315-2.0-T	706-9212
'J'	3 metres	Black	White	Z3-J-F/G-1/0.315-3.0-T	163-3477
'T'	2 metres	Brown	White	Z3-T-F/G-1/0.315-2.0-T	707-6149