

Ultraslim Link Triphosphor Fittings



- Ultraslim fluorescent fittings for all manner of display lighting, particularly kitchen cabinets
- White plastic or aluminium construction with on/off rocker switch
- Universal mounting brackets
- IP20 rated
- Each fitting supplied with 1 x T4 fluorescent tube (3400K)
- Up to 6 fittings can be linked to a 6-way connector block
- 6-way connector block comes complete with 2m mains cable and 3 amp fused plug
- Various lengths of link lead available to run between fittings and connector blocks
- Fitting dimensions (H x D): 43 x 19mm

601067

Watts	Length	Order Code	Price Each		
			1+	5+	10+
White Plastic Fittings					
6W	270mm	177-4181 ●	7.81	7.49	7.21
10W	390mm	177-4178 ●	9.49	9.12	8.77
16W	520mm	177-4179 ●	10.56	10.17	9.75
20W	620mm	177-4180 ●	12.25	11.78	11.30
Spare Tubes					
6W	220mm	177-4184 ●	2.96	2.86	2.74
10W	341mm	177-4185 ●	3.33	3.18	3.06
16W	468mm	177-4186 ●	3.86	3.72	3.57
20W	567mm	177-4187 ●	4.12	3.95	3.80
Accessories					
Link Lead	250mm	177-4183 ●	1.59	1.52	1.46
Link Lead	1m	177-4182 ●	2.12	2.04	1.97