



Sample photo

Order symbol: AR664CHL
Product nbr: 8561021
Description: PC Enclosure
Remarks: Hinged opaque cover
w/Plastic quick release latch

EAN: 6418074066879
El. number:
Finland:
:
Norway:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:		Length	Width	Height	Rating:
mm:		152	152	102	Ingress Protection (EN 60529): IP 66/67
inch:		6.0	6.0	4.0	Impact Resistance (EN 62262): IK 08/07
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Cover screws material:		Stainless steel			
Gasket material:		Polyurethane			
Temperatures:					
Short term:		-40 ... 140 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 284 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
APBP66		PVC Back Panel			
ABP66		Painted Steel Back Panel			
ALBP66		Aluminum Back Panel			
ADFP66		Dead Front Panel w/ screws			
ASP66		Aluminum Swing Panel			
ASPK66		Swing Panel Kit incl. Panel			
ASPHK6		Swing Panel Kit w/o Panel			
AMFL6		6" Mounting Flange Set			
Certificates:		Underwriters Laboratories			

