

WI 04.01 ISSUE 1.2

DESCRIPTION:		CUSTOMER: CPC				SPEC NO:		
CX165DB 75 OHM COAX		REVISION: KEITH GRIFFITHS				610085		
SAP OP CODE	SAP WORK CENTRE	SAP STOCK	TOOL TIP	DIE	NO OF PARTS	LL	DIAM (MM)	
SUB-SHEATH	FSH01 (LINE 8)				1KM		9.15	
		See Relevant DataSheet	Tooling		1		10.35	
CONTROL	TST03							
SHEATH	FSH01 (LINE 8)	See Relevant DataSheet	Tooling		1		11.80	
							INSTRUCTIONS	
							MATERIAL	KG/KM
							75 OHM FOAMED COAXIAL, TAPED & BRAIDED	67.77
							NOM = 0.60MM; MIN =0.50MM	18.00
							PE	
							COLOUR = NATURAL	
							<b>55 MTRS SAMPLE FOR QC TESTS. SEE NOTES</b>	
							+/-0.10MM NOM=0.70MM MIN=0.60MM	24.00
							PE	
							THEORETICAL WEIGHT OF CABLE	109.77
							ACTUAL WIEGHT OF CABLE (03/00)	

AUTHORITY STANDARDS: