

USB to VGA Adapter - External USB Video Graphics Card for PC and MAC- 1920x1200

StarTech ID: *USB2VGAPRO2*



The USB2VGAPRO2 USB to VGA Adapter functions as an external graphics card for Windows® and Mac® computers - the perfect solution for turning your desktop or laptop computer into a dual or multi-monitor environment, all through the simplicity and convenience of USB.

The USB-VGA Adapter delivers high quality video (up to 1920x1200) for a variety of applications and is capable of simultaneously running up to five additional displays from a single computer (using four USB2VGAPRO2 External Video Adapters). The adapter connects to a host computer through a USB 2.0 port, acting as an external VGA video card to either extend or mirror the desktop shown on the existing display - without having to open the computer case.

Featuring driver support for Microsoft Windows® (including Aero themes) and Mac OS X, and with video support for resolutions up to 1920x1200, this USB-VGA video adapter is the ideal solution for a wide range of operating environments as well as large-screen displays/monitors.

The USB2VGAPRO2 USB to VGA Adapter is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Add multiple (up to five) monitors / projectors to your computer setup using one USB2DVIPRO2 device for each additional display
- View large or multiple spreadsheets across multiple displays
- Increase productivity by running multiple applications on different DVI screens; check your email on one display while editing a document on the other
- Use the USB-DVI adapter to connect your PC to your television for showing family pictures and movies
- Connect multiple DVI monitors to a single computer to create engaging multimedia presentations
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Features

- Optimal performance at 1920x1200 and ideal for use with 24" to 26" monitors or smaller
- Support for Aero themes in Windows®
- Works with Mac® OS X
- Connect up to five adapters to one PC for a true extended desktop experience
- USB-Powered operation, no external power adapter required
- Quick and easy installation
- Powered by DisplayLink DL-195 chip

Technical Specifications

Warranty	2 Years
Memory	16MB
Chipset ID	DisplayLink - DL-195
Connector Type(s)	1 - USB A (4 pin) Male
Connector Type(s)	1 - VGA (15 pin; High Density D-Sub) Female
Maximum Analog Resolutions	1920x1200 (32-bit Color)
Supported Resolutions	Standard(16/32 bit): 640x480, 800x600, 1280x1024, 1600x1200
	Widescreen(16/32 bit): 1024x768, 1366x768, 1440X900, 1680x1050, 1920x1200
OS Compatibility	Windows® 8 (32/64bit), 7 (32/64bit), Vista(32/64), XP(32), 2000 (Aero 3D interface supported) Mac OS® Mountain Lion (10.8), Lion (10.7) Snow Leopard (10.6), Leopard (10.5), Tiger (10.4)
Color	Black
Product Length	78 mm [3.1 in]
Product Width	43.5 mm [1.7 in]
Product Height	15.5 mm [0.6 in]
Product Weight	300 g [10.6 oz]
LED Indicators	1 - Blue - Power
Power Adapter Included	USB Powered
Operating Temperature	10°C to 40°C (50°F to 104°F)
Storage Temperature	-10°C to 80°C (14°F to 176°F)
Humidity	<85% non-condensing
System and Cable Requirements	1.2Ghz or higher CPU 30MB of hard drive space 512 MB RAM USB 2.0 Port
Note	Power PC-based Macintosh computers, such as late-model iMacs, PowerBooks and PowerMacs, are not currently supported
Shipping (Package) Weight	240 g [8.5 oz]
Included in Package	1 - USB to VGA Adapter
Included in Package	1 - Driver CD

Included in Package 1 - Instruction Manual

Certifications, Reports and Compatibility

