

Price*: 98.00 USD

Nato products



Main

Commercial Status	Commercialised
Range of product	9050JCK
Product or component type	Timer
[In] rated current	10 A
Switch function	DPDT
Contacts type and composition	2 NO + 2 NC
Control circuit voltage	24 V AC/DC
Maximum switching voltage	240 V AC
Mounting support	Socket
Pin number	11
Shape of pin	Tubular
Product certifications	CE CSA UL listed
Time delay type	Off-delay
Time delay range	0.1...10 s

Ordering and shipping details

Category	21651 - 9050 JCK(NOT JCK60, 70) G P TIMERS
Discount Schedule	CP2
GTIN	00785901032731
Nbr. of units in pkg.	1
Package weight(Lbs)	0.33
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0627 - Schneider Electric declaration of conformity

Contractual warranty

Period	18 months
--------	-----------