



Main

| | |
|---------------------------|----------------------|
| Commercial Status | Commercialised |
| Range of product | Harmony XVE Optimum |
| Product or component type | Base unit with cover |
| Kit composition | Base unit Cover |
| Component name | XVE |

Complementary

| | |
|-------------------------------|--|
| Mounting diameter | 2.76 in (70 mm) |
| Assembly style | Customer assembly |
| Marking | CE |
| Terminals description ISO n°1 | (COM-1)PW (COM-2)PW (COM-3)PW (COM-4)PW (COM-5)PW (GND)GROUND |
| Product weight | 0.24 lb(US) (0.11 kg) |

Environment

| | |
|--|--|
| Standards | EN/IEC 60947-1 EN/IEC 60947-5-1 |
| Product certifications | CCC CSA UL |
| Ambient air temperature for storage | -40...158 °F (-40...70 °C) |
| Ambient air temperature for operation | -13...131 °F (-25...55 °C) |
| Class of protection against electric shock | Class I plastic tube mounting conforming to IEC 61140 Class I aluminium tube mounting conforming to IEC 61140 |
| Protective treatment | TC |
| IP degree of protection | IP42 (indoor) conforming to IEC 60529 |

Ordering and shipping details

| | |
|-----------------------|---------------------------------|
| Category | 22616 - XVE OPTIMUM STACKLIGHTS |
| Discount Schedule | XV |
| GTIN | 00785901665069 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.26 |
| Returnability | Y |
| Country of origin | CZ |