



### Main

|                                    |                     |
|------------------------------------|---------------------|
| Commercial Status                  | Commercialised      |
| Range of product                   | Harmony XVE Optimum |
| Product or component type          | Indicator bank      |
| Beacon or indicator bank unit type | Illuminated unit    |
| Signalling type                    | Steady              |
| Component name                     | XVE                 |
| Light source                       | Red integral LED    |
| Bulb type                          | LED                 |
| [Us] rated supply voltage          | 24 V AC/DC          |

### Complementary

|  |  |
|--|--|
| Mounting diameter                      | 2.76 in (70 mm)  |
| Assembly style                         | Customer assembly  |
| Connections - terminals                | Screw clamp terminals: <= 1 x 1.5 mm <sup>2</sup> with cable end |
| Marking                                | CE   |
| Overld and short-circuit prot          | 0.63 A   |
| [Ui] rated insulation voltage          | 250 V conforming to IEC 60947-1                                  |
| Nominal voltage limit                  | 0.85...1.1 Un conforming to IEC 60947-5-1                        |
| Current consumption                    | < 25 mA  |
| [Uimp] rated impulse withstand voltage | 4 kV conforming to IEC 60947-1                                   |
| Luminance                              | 74.32 fc (800 cd/m <sup>2</sup> )                                |
| CAD overall width                      | 2.76 in (70 mm)  |
| CAD overall height                     | 2.05 in (52 mm)  |
| CAD overall depth                      | 2.76 in (70 mm)  |
| Product weight                         | 0.17 lb(US) (0.077 kg)   |

### Environment

|  |  |
|--|--|
| Standards                                  | EN/IEC 60947-1<br>EN/IEC 60947-5-1   |
| Product certifications                     | CCC<br>CSA<br>UL   |
| Ambient air temperature for storage        | -40...158 °F (-40...70 °C)   |
| Ambient air temperature for operation      | -13...131 °F (-25...55 °C)   |
| Class of protection against electric shock | Class I plastic tube mounting conforming to IEC 61140<br>Class I aluminium tube mounting conforming to IEC 61140           |
| Protective treatment                       | TC   |
| IP degree of protection                    | IP42 in vertical position conforming to IEC 60529<br>IP40 in any position except vertical position conforming to IEC 60529 |

Ordering and shipping details

|                       |                                 |
|-----------------------|---------------------------------|
| Category              | 22616 - XVE OPTIMUM STACKLIGHTS |
| Discount Schedule     | XV                              |
| GTIN                  | 00785901434405                  |
| Nbr. of units in pkg. | 1                               |
| Package weight(Lbs)   | 0.17                            |
| Returnability         | Y                               |
| Country of origin     | CZ                              |