

Model 1026

Provides a variety of functions: megohmmeter, DC voltmeter, AC voltmeter, ohmmeter and continuity testing

► SPECIFICATIONS

MODEL	1026	
INSULATION TESTS		
Test Voltage	250V 500V 1000V	1kΩ to 4000MΩ 1kΩ to 4000MΩ 1kΩ to 4000MΩ
Accuracy	<2000MΩ ≥2000MΩ	±3% of Reading + 5cts ±5% of Reading + 5cts
RESISTANCE TESTS		
Measurement Range	Auto ranging to 4000Ω	
Resolution	0.1 to 1Ω	
Accuracy	±1% of Reading + 5cts	
CONTINUITY TESTS		
Measurement Range	Displays and beeps below 40Ω	
Active	≤40Ω	
Protection	600Vrms	
VOLTAGE TESTS		
AC VOLTAGE		
Measurement Range	0 to 600V	
Accuracy	±1.5% of Reading + 5cts	
DC VOLTAGE		
Measurement Range	0 to 600V	
Accuracy	±1% of Reading + 3cts	
ELECTRICAL		
Power Source	Eight 1.5V AA Alkaline batteries (included)	

► PRODUCT INCLUDES

Test leads, alligator clips, batteries, soft carrying case and user manual.



► FEATURES

- Test voltage selections of 250V, 500V and 1000V
- Insulation measurements to 4000MΩ
- Resistance measurements to 4000Ω
- Continuity test
- Continuity beeper
- 600VAC/DC test voltage range
- Large, easy-to-read digital display
- Data hold switch
- Test button may be “locked-on” for three minutes for hands-free operation
- Automatic discharge when test button is released
- Low battery indicator
- Includes test leads and soft carrying case
- EN 61010-1, 1000V CAT II, 600V CAT III

CATALOG NO.	DESCRIPTION
2117.72	Megohmmeter Model 1026 (Digital, 250V, 500V, 1000V, 4000Ω, V)