

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130109-0028](#)
Status: **Active**
Description: Pro-Yellow® Nylon 26W Fluorescent Hand Lamp with Switch and Grips Molded, Cord Type 18/3 SJTW, Cord Length 7.62m (25.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

UL E59049

General

Product Family	Portable Lighting
Series	130109
NEMA Configuration	NEMA 5-15
Outlet	None
Product Literature Order No	987650-8053
Product Name	Pro-Yellow®
Type	Hand Lamps
UPC	78678851149
Woodhead	Yes

Physical

Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Depth	N/A
Duty	Commercial
Guard Included	No
Guard Type	N/A
Height	N/A
Length	N/A
Material - Guard	Polycarbonate
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Fluorescent
Cord Type - Primary	18/3 SJTW
Lamp Type	PL-C 26/41/4P
Lamp Wattage - Maximum	26W
Lumens	1800
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info

Old Part Number WT6F-25



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

**REACH SVHC
Not Reviewed**

**Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130109Series](#)