


# HC-EVO-B10-HHWD-PLBK

Order No.: 1407631

<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1407631>

HEAVYCON EVO sleeve housing, plastic, with bayonet flange for EVO screw connection, B10, with double locking latch, height: mm, without EVO screw connection

| Commercial data        |  |
|------------------------|--|
| EAN                    | <br>4 046356 776936 |
| Pack                   | 1  |
| Customs tariff         | 85389099   |
| Gross weight in pieces | 22.22 g  |
| Country of Origin      | PL   |

**Product notes**

WEEE/RoHS-compliant since:  
03/07/2012



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

| Technical data      |  |
|---------------------|--|
| <b>General data</b> |  |
| Note                | For contact inserts HC-B10, BB18, DD42, M, K8/24 |
| Design              | B10  |
| Height              | 87.5 mm  |
| Width               | 44 mm  |

|   |  |
|---|--|
| Length                                  | 73 mm  |
| Housing type                            | Sleeve housings  |
| Color                                   | black  |
| Locking type                            | With double locking latch  |
| No. of cable exits                      | 1  |
| Cable exit                              | Straight   |
|   | Lateral  |
| Protective cover                        | No   |
| Degree of protection for housing        | IP65   |
| Ambient temperature (operation)         | -40 °C ... 125 °C  |
| Housing material                        | Polyamide  |
| Material lock                           | Polyamide  |
| Inflammability class according to UL 94 | V0   |
| Connection                              | The sleeve base housing must be supplemented with the EVO screw connection. The EVO screw connection is available in four sizes. It facilitates the creation of a straight or a side cable outlet. The EVO screw connection is mounted with the aid of, for example, a pipe wrench |

### Certificates

Certification

Certifications applied for:


Certification Ex:

### Accessories

| Item           | Designation      | Description   |
|----------------|------------------|---|
| <b>General</b> |                  |   |
| 1407669        | HC-B-G-M20-PLRBK | EVO plastic cable gland with bayonet locking; size M20  |
| 1407670        | HC-B-G-M25-PLRBK | EVO plastic cable gland with bayonet locking; size M25  |
| 1407671        | HC-B-G-M32-PLRBK | EVO plastic cable gland with bayonet locking; size M32  |
| 1407672        | HC-B-G-M40-PLRBK | EVO plastic cable gland with bayonet locking; size M40  |
| <b>Marking</b> |                  |   |
| 0829439        | US-EMP (20X9)    | Snap-in markers, Card, white, Unlabeled, Can be labeled with: Thermomark C+, Thermomark C, Mounting type: Snapped into marker carrier, Lettering field: 20 x 9 mm |

## Drawings

Dimensioned drawing



Dimensional drawing

**Address**

PHOENIX CONTACT Ltd  
Halesfield 13  
Telford / Shropshire / TF7 4PG,England  
Phone 01952 681 700  
Fax 01952 681 799  
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.  
Technical modifications reserved;