


# HC-B-G-M25-PLRBK

Order No.: 1407670

<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1407670>

EVO plastic cable gland with bayonet locking; size M25

**Commercial data**

EAN	 4 046356 776387
Pack	1
Customs tariff	39269097
Gross weight in pieces	40.72 g
Country of Origin	PL

**Product notes**WEEE/RoHS-compliant since:  
03/07/2012

Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

**Technical data****General data**

Type of the screw connection	1x M25
Cable gland material	Polyamide
Seal material	NBR
Cable seal material	NBR
Wrench size, union nut	26 mm
Thread type connection side 1	Bayonet

External cable diameter	9 mm ... 17 mm
Tightening torque, union nut	6.00 Nm
Inflammability class according to UL 94	V0
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 100 °C

### Certificates


Certification

Certifications applied for:

Certification Ex:

### Drawings

Dimensioned drawing



Dimensional drawing

**Address**

PHOENIX CONTACT Ltd  
Halesfield 13  
Telford / Shropshire / TF7 4PG,England  
Phone 01952 681 700  
Fax 01952 681 799  
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.  
Technical modifications reserved;