

HC-B-G-M40-PLRBK

Order No.: 1407672

<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1407672>

EVO plastic cable gland with bayonet locking; size M40

Commercial data

EAN	 4 046356 776400
Pack	1
Customs tariff	39269097
Gross weight in pieces	65.30 g
Country of Origin	PL

Product notesWEEE/RoHS-compliant since:
03/07/2012

Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General data**

Type of the screw connection	1x M40
Cable gland material	Polyamide
Seal material	NBR
Cable seal material	NBR
Wrench size, union nut	36 mm
Thread type connection side 1	Bayonet

External cable diameter	19 mm ... 28 mm
Tightening torque, union nut	17.00 Nm
Inflammability class according to UL 94	V0
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 100 °C

Certificates


Certification

Certifications applied for:

Certification Ex:

Drawings

Dimensioned drawing



Dimensional drawing

Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG,England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;