

### Product Search

Item no...

### Product Catalog

#### Products

#### Lamps & LED-Lamps

#### LED lamps

#### StarLEDs

#### BA9s - T-3 1/4

BA9s, Multivoltage  
BA9s, flashing

### Markets

#### Automotive

#### Aviation

#### Gaming

#### Illumination

#### Transport

#### Custom Projects

## Product details

Article: 18600150



**StarLED, BA9s LED-Lamp, 6V AC/DC, red**

### Description

Designation: StarLED, BA9s LED-Lamp, 6V AC/DC, red

Product range: StarLED

### Optical features

Colour: red

Dominant Wavelength: 630 nm

Number of LEDs: 1

Typ. Luminous intensity: 400 mcd (at DC current)

### Electrical features

Operating Voltage: 6 V

Voltage type: AC/DC

Rectifier: Half wave

Voltage tolerance: 10 %

DC current: 17 mA

### Mechanical features

Socket: BA9s

Lamp size: T-3 1/4

Length: 25 mm

Diameter: 10 mm

### Thermal features

Operating temperature: -20...+60 °C

Storage temperature: -25...+80 °C

### Gallery

### Latest News

**2013-01-08**  
LEDS MADE EASY.  
>> [More details](#)

**2012-03-09**  
Successful surveillance audit according to ISO 9001:2008  
>> [More details](#)

**2012-02-24**  
Latest Nichia LEDs in CML products  
>> [More details](#)



[Standard Image](#)

[Drawing](#)

Click on a small picture to select it. Click the large image to view full size.

