



Product Search

Item no...

Product Catalog

Products

Lamps & LED-Lamps

LED lamps

StarLEDs

BA9s - T-3 1/4

- BA9s, Multivoltage
- BA9s, flashing

Markets

Automotive

Aviation

Gaming

Illumination

Transport

Custom Projects

Product details

Article: **1860015W3**



StarLED, BA9s LED-Lamp, 6V AC/DC, cold white

Description

Designation: StarLED, BA9s LED-Lamp, 6V AC/DC, cold white

Product range: StarLED

Optical features

Colour: cold white

Coordinates in colour 0,31 / 0,32

Number of LEDs: 1

Typ. Luminous intensity: 500 mcd (at DC current)

LED epoxy type: clear

Electrical features

Operating Voltage: 6 V

Voltage type: AC/DC

Rectifier: Half wave

Voltage tolerance: 10 %

Mechanical features

Socket: BA9s

Lamp size: T-3 1/4

Length: 25 mm

Diameter: 10 mm

Thermal features

Operating temperature: -20...+60 °C

Storage temperature: -25...+80 °C

Gallery

Latest News

2013-01-08
LEDS MADE EASY.
>> [More details](#)

2012-03-09
Successful surveillance audit according to ISO 9001:2008
>> [More details](#)

2012-02-24
Latest Nichia LEDs in CML products
>> [More details](#)



[Standard Image](#)

[Drawing](#)

Click on a small picture to select it. Click the large image to view full size.

 **Multivoltage LED Lamps**
Covering the voltage range of 6 to 32V
Available in all colours and BA9s socket

