

### Product Search

Item no...

### Product Catalog

- Products
- Lamps & LED-Lamps
- LED lamps
- StarLEDs
- BA9s - T-3 1/4**
  - BA9s, Multivoltage
  - BA9s, flashing

### Markets

- Automotive
- Aviation
- Gaming
- Illumination
- Transport
- Custom Projects

## Product details

**Article: 1860275W3D**



**StarLED, BA9s LED-Lamp, 60V AC/DC, cold white**

### Description

Designation: StarLED, BA9s LED-Lamp, 60V AC/DC, cold white  
 Product range: StarLED

### Optical features

Colour: cold white  
 Coordinates in colour 0,31 / 0,32  
 Number of LEDs: 1  
 Typ. Luminous intensity: 150 mcd (at DC current)  
 LED epoxy type: diffused

### Electrical features

Operating Voltage: 60 V  
 Voltage type: AC/DC  
 Rectifier: Bridge  
 Voltage tolerance: 10 %

### Mechanical features

Socket: BA9s  
 Lamp size: T-3 1/4  
 Length: 25 mm  
 Diameter: 10 mm

### Thermal features

Operating temperature: -20...+60 °C  
 Storage temperature: -25...+80 °C

### Gallery

### Latest News

- 2013-01-08**  
LEDS MADE EASY.  
[» More details](#)
- 2012-03-09**  
Successful surveillance audit according to ISO 9001:2008  
[» More details](#)
- 2012-02-24**  
Latest Nichia LEDs in CML products  
[» More details](#)



[Standard Image](#)

[Drawing](#)

Click on a small picture to select it. Click the large image to view full size.

 **LED Lamps according to EN 50155**  
Designed for rolling stock applications  
Long life time including safety feature

