



## Product Search

Item no...

## Product Catalog

### Products

#### Lamps & LED-Lamps

#### LED lamps

#### Mega StarLEDs

#### BA15s - 3x3mm LEDs

## Markets

#### Automotive

#### Aviation

#### Gaming

#### Illumination

#### Transport

#### Custom Projects

## Product details

Article: 1863335W3



**Mega StarLED, BA15s LED-Lamp, 24V AC/DC, cold white**

### Description

**Designation:** Mega StarLED, BA15s LED-Lamp, 24V AC/DC, cold white

**Description:** Mega StarLEDs are equipped with more than one LED. Consequently, higher brightness and better light distribution can be achieved.

**Manufacturer:** CML Technologies GmbH & Co. KG

**Item status:** available

**Application:** Industry

**Product range:** Mega StarLED

### Optical features

**Colour:** cold white

**Coordinates in colour:** 0,31 / 0,32

**Number of LEDs:** 3

**Typ. Luminous intensity:** 3 x 2100 mcd (at DC current)

**LED epoxy type:** clear

**Comment:** Due to manufacturing tolerances of the LEDs may be slight variations in color (color temperature).

### Electrical features

**Operating Voltage:** 24 V

**Voltage type:** AC/DC

**Rectifier:** Bridge

**Voltage tolerance:** 10 %

**Current:** 7 mA

### Mechanical features

**Socket:** BA15s

**Material plastic:** Makrolon 2805

**Lamp size:** T-5

## Latest News

**2013-01-08**  
LEDS MADE EASY.  
>> [More details](#)

**2012-03-09**  
Successful surveillance audit according to ISO 9001:2008  
>> [More details](#)

**2012-02-24**  
Latest Nichia LEDs in CML products  
>> [More details](#)

Length: 35 mm  
Diameter: 16 mm

### Thermal features

---

Operating temperature: -20...+60 °C  
Storage temperature: -25...+80 °C

### Gallery

---



[Standard Image](#)

[Drawing](#)

[Image](#)

Click on a small picture to select it. Click the large image to view full size.

 **LED Lamps according EN 50155**  
Designed for rolling stock applications  
Long life time including safety feature

