

Product Search

Item no...

Product Catalog

- Products**
- Lamps & LED-Lamps
- LED lamps
- Mega StarLEDs
- BA15s - 3x3mm LEDs

Markets

- Automotive
- Aviation
- Gaming
- Illumination
- Transport
- Custom Projects

Product details

Article: 1863335W3D



Mega StarLED, BA15s LED-Lamp, 24V AC/DC, cold white

Description

Designation: Mega StarLED, BA15s LED-Lamp, 24V AC/DC, cold white
Description: Mega StarLEDs are equipped with more than one LED. Consequently, higher brightness and better light distribution can be achieved.
Manufacturer: CML Technologies GmbH & Co. KG
Item status: available
Application: Industry
Product range: Mega StarLED

Optical features

Colour: cold white
Coordinates in colour: 0,31 / 0,32
Number of LEDs: 3
Typ. Luminous intensity: 3 x 1050 mcd (at DC current)
LED epoxy type: diffused
Comment: Due to manufacturing tolerances of the LEDs may be slight variations in color (color temperature).

Electrical features

Operating Voltage: 24 V
Voltage type: AC/DC
Rectifier: Bridge
Voltage tolerance: 10 %
Current: 7 mA

Mechanical features

Socket: BA15s
Material plastic: Makrolon 2805
Lamp size: T-5

Latest News

- 2013-01-08**
 LEDS MADE EASY.
 >> [More details](#)
- 2012-03-09**
 Successful surveillance audit according to ISO 9001:2008
 >> [More details](#)
- 2012-02-24**
 Latest Nichia LEDs in CML products
 >> [More details](#)

Length: 35 mm
Diameter: 16 mm

Thermal features

Operating temperature: -20...+60 °C
Storage temperature: -25...+80 °C

Gallery



[Standard Image](#)

[Drawing](#)

[Image](#)

Click on a small picture to select it. Click the large image to view full size.



Flashing BA9s LED Lamps
You need a flashing switch in your application?
Just exchange the lamp and its done !

