

PV-CMA-S03-6/1,1

Order No.: 1459964

<http://eshop.phoenixcontact.net/phoenix/treeViewClick.do?UID=1459964>

Photovoltaic cable (assembled), Nominal current: 40 A, Color: black

Commercial data

EAN	 4 046356 607810
Note	Made-to-order
Pack	1 pcs.
Customs tariff	85446010
Gross weight in pieces	0.1078 KG
Net weight per piece (exclusive packing)	0.1078 KG

Product notesWEEE/RoHS-compliant since:
08/02/2010

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**Technical data**

Rated voltage	1500 V
Nominal cross section	6 mm ²
Protection class	II
Ambient temperature (operation)	-40 °C ... 85 °C (Plug / socket)

Material properties

Color	black
Insulating material	PA 6
Contact material	Cu
Contact surface material	Sn
Inflammability class according to UL 94	V0

Connection data

Contact resistance with connected conductor	0.3 mΩ
Cable type	PV1-F cables

General data

Design	Male connector
--------	----------------

Certificates / Approvals



Certification VDE Zeichengenehmigung

Certifications applied for:

Certification Ex:

Accessories

Item	Designation	Description
General		
1785430	PV-C PROTECTION CAP	Protective cap for SUNCLIX photovoltaic connector; degree of protection: IP67
1207637	QUICK WIREFOX 6 SC	Stripping tool for short-circuit proof conductors, stripping range: 1.5 up to 6 mm ² , wire cutting up to 6 mm ² cable stopper up to 18 mm ²
Tools		
1204517	SZF 1-0,6X3,5	Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford Shropshire TF7 4PG,GB
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



© 2013 Phoenix Contact
Technical modifications reserved;