



Features & Benefits

- ✘ Suitable for Gigabit Ethernet applications
- ✘ Shallow design requires minimal back-box depth
- ✘ Interchangeable with all other Euro modules and quarter blanks
- ✘ Fits all standard Euro faceplates
- ✘ Individually QA tested



Ordering Information

Product Description	Part Number
Category 6 Compact UTP RJ45 Euro Module	008-000-001-20
For Euro Faceplate options please see page 46	

Specification

Width	25mm
Depth	21mm
Height	50mm
Back-box Depth	Minimum 15mm recommended
Material	Polycarbonate/ABS thermoplastic resin, with grade UL94 V0 at 1.5mm flame retardency
Finish	High gloss
IDC Labels	Individual colour coded to T568B
IDC Blocks	4 Way Industry Standard IDC blocks
Conforms to	TIA/EIA-568-B Category 6 specification

The Connectix Category 6 compact module is designed to provide one of the shallowest wall outlets on the market. They are the ideal solution wherever back-box depth is a problem.

The attractive high gloss finish and easy to use labelling system are identical to all other Connectix Cabling Systems Modules, making them interchangeable in most applications.

Category 6 Compact Modules can be fitted into Single or Dual gang Euro faceplates and can be combined with quarter blanks and/or voice modules to provide the required configuration.

Connectix Category 6 modules are fully compliant with the TIA/EIA Category 6 standard. When used in conjunction with Category 6 patch panels and UTP cable the user will get a link performance exceeding the Category 6 requirements.

The Category 6 module is identical in appearance to other modules in the Connectix Cabling Systems range, making a seamless transition to Category 6 a reality

