



Features & Benefits

- ✘ High Density, Single Gang 4 Port
- ✘ Enhanced Category 5 Performance
- ✘ No protruding leads
- ✘ Designed for direct wall mounting
- ✘ Custom logo service available
- ✘ Also available in a 2 port version

The Connectix 4000 series offers Enhanced Category 5 performance in a high-density package. The position of the sockets allow for a compact installation without protruding leads.

The Connectix 4000 series is extremely quick and easy to install. Just attach the base plate, snap in the PCB, punch down the cables and install the cover. Gone are the problems of installing modules into a faceplate and pushing excess wires in a back box.

The 4000 series outlets have been designed for direct wall mounting with top entry mini trunking, and an optional spacer plate provides side cable entry. In addition, they fit on a standard back box to provide maximum mounting flexibility.

Ordering Information

Product Description	Part Number
4010 4 Way Enhanced Cat 5 Shuttered Outlet	008-001-010-05
4020 4 Way Enhanced Cat 5 Vertical Wall Outlet	008-001-011-01
4022 2 Way Enhanced Cat 5 Vertical Wall Outlet	008-001-011-03
4100 Entry Spacer plate	008-001-013-01

Specification

Width	87mm
Depth	27mm
Height	87mm
Spacer Plate Depth	8mm
Material	ABS thermoplastic resin, with grade UL94 VO at 1.5mm flame retardancy
Finish	High Gloss
IDC Blocks	4 Way Industry Standard IDC blocks
PCB	1.6mm double sided PTH Boards
Conforms to	TIA/EIA-568-B Enhanced Category 5 Specification

Simple Assembly Sequence

