

## PG Glands (Size 16)



Straight Plastic Short Thread



Straight Plastic With Flex Spring



Straight Conduit Adapter Thread



Straight Conduit Push-in



Right Angle

## Features

- Maximize cable pullout strength



- Housing and sealing gland materials designed for use in the toughest environmental conditions



- All materials are RoHS compliant



- Waterproof to 5 bar of pressure IP68



# PG Glands

## (Size 16)

<b>APP P/N</b>	<b>Cable Range Wire Outer Dia. mm (in)</b>
PS1P16-10X	11.2 - 5.5 (0.44 - 0.22)
PS1P16-14X	14.1 - 8.0 (0.56 - 0.31)
PF1P16-10X	11.2 - 5.5 (0.44 - 0.22)
PF1P16-13X	13.8 - 8.0 (0.54 - 0.31)
PR7P16-10X	11.0 - 7.0 (0.43 - 0.28)
PR7P16-13X	13.0 - 8.0 (0.51 - 0.31)
PS2P16-3X	3.5 - 2.5 (0.14 - 0.10)
PS2P16-4X	4.3 - 3.3 (0.17 - 0.13)
PS2P16-6X	6.1 - 4.3 (0.24 - 0.17)
PS3P16-3X	3.6 - 2.6 (0.14 - 0.10)
PS3P16-5X	5.2 - 3.5(0.20 - 0.14)
PS4P16-2X	2.5 - 1.6 (0.10 - 0.06)
PS4P16-3X	3.6 - 2.5 (0.14 - 0.10)
PS4P16-4X	4.8 - 3.4 (0.19 - 0.13)
PS5P16-2X	2.1 - 1.3 (0.08 - 0.05)
PS5P16-3X	3.1 - 2.0 (0.12 - 0.08)
PS5P16-4X	4.1 - 3.0 (0.16 - 0.12)
PS6P16-2X	2.0 - 1.3 (0.08 - 0.05)
PS6P16-3X	3.0 - 2.0 (0.16 - 0.08)

<b>APP P/N</b>	<b>Conduit O. D. mm (in)</b>
CAP16-15X	15.8 (0.62)
CAP16-18X	18.5 (0.73)
CAP16-21X	21.2 (0.83)
CAP16-28X	28.5 (1.22)
CT1P16-15X	15.8 (0.62)
CT1P16-18X	17.8 (0.70)
CT1P16-21X	21.2 (0.83)