

19" CABINETS

CamRack-QX



Flat packed- Assembled in **3 minutes!**

19" Wall mounted cabinets, designed for cabling, telecommunications, IT and industrial and home installations

- Delivered flat packed for ease of access to all installations. Also reduces associated logistic costs and offers greater protection during transit
- Fast and efficient 3 minute assembly **without tools**
- 2x 19" mounting profiles. Variable depth, in 20mm increments
- Fast fixings 1/4 turn locks
- Quick release door. Tempered, smokey safety glass
- Easily removable side panels with 2x 1/4 turn locks
- Easily drilled plastic blanking covers for cable entry
- Template for wall mounting, included
- Maximum recommended load capacity: 45kg


Finishes: Epoxy paint, Ral 7016

Delivery: Flat packed with carrying handle



RED	BLUE	ORANGE	WHITE	BLACK	U	WIDTH	DEPTH	HEIGHT
CQX064211	CQX064212	CQX064213	CQX064214	CQX064215	6U	580mm	421mm	384mm
CQX094211	CQX094212	CQX094213	CQX094214	CQX094215	9U	580mm	421mm	517mm
CQX125211	CQX125212	CQX125213	CQX125214	CQX125215	12U	580mm	521mm	651mm
CQX155211	CQX155212	CQX155213	CQX155214	CQX155215	15U	580mm	521mm	784mm
CQX186211	CQX186212	CQX186213	CQX186214	CQX186215	18U	580mm	621mm	917mm

• **Standard corner colours:**



• **Other corner colours available upon request:**

