


Front panels, U profile, shieldable



Product illustrations are exemplary illustrations and can deviate from supplied products.

Part no.: 30848-354

Features:

- High stability through U profile
- Front panel, U profile, Al, front anodised, rear conductive, 2 alignment pins pressed-in, stainless steel
- Differences in the finish between 2 ... 12 HP and 14 ... 84 HP

Add to basket




Standard pack quantity 5



Technical Information:

Description	Height	Width	Height	B
Front panels, U profile, shieldable	3 U	4 HP	128.4 mm	20 mm

Downloads:

Download CAD data in DWG/DXF/PDF format ([Log in](#) required) 

To gain access to the additional information you must [log in](#).
If you do not yet have a user name, you may [register here](#).

Accessories:

Part no.	Description	
21101-853	Textile EMC gasket 3 U, PU 10 pieces	Add to basket
21101-854	Textile EMC gasket 3 U, PU 100 pieces	Add to basket

Note:

- Standard pack quantity:
2 to 28 HP: 5 pieces,
42 to 84 HP: 1 piece,
supplied in standard pack quantities (SPQ) only
- Please order EMC profile seal and fixing materials separately