


## Front panels, U profile, shieldable



Product illustrations are exemplary illustrations and can deviate from supplied products.

**Part no.: 30848-380**

### Features:

- High stability through U profile
- Front panel, U profile, Al, front anodised, rear conductive, 2 alignment pins pressed-in, stainless steel
- Differences in the finish between 2 ... 12 HP and 14 ... 84 HP

Add to basket




**Standard pack quantity 5**



### Technical Information:

Description	Height	Width	Height	B
Front panels, U profile, shieldable	3 U	6 HP	128.4 mm	30.1 mm

### Downloads:

Download CAD data in DWG/DXF/PDF format ([Log in](#) required) 

To gain access to the additional information you must [log in](#).  
If you do not yet have a user name, you may [register here](#).

**Accessories:**

<b>Part no.</b>	<b>Description</b>	
<b>21101-853</b>	Textile EMC gasket 3 U, PU 10 pieces	<b>Add to basket</b>
<b>21101-854</b>	Textile EMC gasket 3 U, PU 100 pieces	<b>Add to basket</b>

**Note:**

- Standard pack quantity:  
2 to 28 HP: 5 pieces,  
42 to 84 HP: 1 piece,  
supplied in standard pack quantities (SPQ) only
- Please order EMC profile seal and fixing materials separately