


# PCB TERMINAL BLOCKS

## 5.08mm Pitch Screwless Pluggable Terminal

- 2-24 pole solid block (female)
- 2-16 pole solid block (male)
- Pluggable female and male connectors
- Also compatible with conventional 5.08mm pluggable terminal blocks
- Screwless - wire retained by cage spring
- Optional mounting clip, CSTB9C can be removed after fitting
- Polarised mouldings
- Moulded in green UL94-V0 flame retardant PA
- 0.2-2.5mm<sup>2</sup> (24-14AWG) solid & stranded cable
-  pending
- GWT compliant version also


### SPECIFICATION

|                           |                            |
|---------------------------|----------------------------|
| Rating                    | 18A/320V                   |
|                           | UL=14A/300V, IMQ=18A/320V  |
| Dielectric strength       | ≥2.5kV                     |
| Impulse withstand voltage | 4kV                        |
| Working temperature       | 110°C                      |
| Moulding                  | UL94-V0 flame retardant PA |
| Clamp/spring              | Nickel copper flash brass  |

### Female connector

| TYPE NO.    | POLES | LENGTH |
|-------------|-------|--------|
| CSTB9208/2  | 2     | 10.2mm |
| CSTB9208/3  | 3     | 15.2mm |
| CSTB9208/4  | 4     | 20.3mm |
| CSTB9208/5  | 5     | 25.4mm |
| CSTB9208/6  | 6     | 30.5mm |
| CSTB9208/7  | 7     | 35.6mm |
| CSTB9208/8  | 8     | 40.6mm |
| CSTB9208/9  | 9     | 45.7mm |
| CSTB9208/10 | 10    | 50.8mm |
| CSTB9208/11 | 11    | 55.9mm |
| CSTB9208/12 | 12    | 61mm   |
| CSTB9208/13 | 13    | 66mm   |


| TYPE NO.    | POLES | LENGTH  |
|-------------|-------|---------|
| CSTB9208/14 | 14    | 71.1mm  |
| CSTB9208/15 | 15    | 76.2mm  |
| CSTB9208/16 | 16    | 81.3mm  |
| CSTB9208/17 | 17    | 86.4mm  |
| CSTB9208/18 | 18    | 91.4mm  |
| CSTB9208/19 | 19    | 96.5mm  |
| CSTB9208/20 | 20    | 101.6mm |
| CSTB9208/21 | 21    | 106.7mm |
| CSTB9208/22 | 22    | 111.8mm |
| CSTB9208/23 | 23    | 116.8mm |
| CSTB9208/24 | 24    | 121.9mm |



### Male connector


| TYPE NO.    | POLES | LENGTH  |
|-------------|-------|---------|
| CSTB9308/2  | 2     | 11.36mm |
| CSTB9308/3  | 3     | 16.44mm |
| CSTB9308/4  | 4     | 21.52mm |
| CSTB9308/5  | 5     | 26.6mm  |
| CSTB9308/6  | 6     | 31.68mm |
| CSTB9308/7  | 7     | 36.76mm |
| CSTB9308/8  | 8     | 41.84mm |
| CSTB9308/9  | 9     | 46.92mm |
| CSTB9308/10 | 10    | 52mm    |
| CSTB9308/11 | 11    | 57.08mm |
| CSTB9308/12 | 12    | 62.16mm |
| CSTB9308/13 | 13    | 67.24mm |

| TYPE NO.    | POLES | LENGTH  |
|-------------|-------|---------|
| CSTB9308/14 | 14    | 72.32mm |
| CSTB9308/15 | 15    | 77.4mm  |
| CSTB9308/16 | 16    | 82.48mm |



### Mounting Clip

TYPE NO.  
CSTB9C



CSTB9308

PCB  
TERMINAL  
BLOCKS

INTER-  
CONNECTION

FUSES &  
FUSE-  
HOLDERS

LEDs &  
INDICATORS

MINIATURE  
SWITCHES

LIMIT &  
SAFETY  
SWITCHES

CONTROL  
PRODUCTS

INTERFACE  
MODULES &  
SUPPORTS

RELAY  
BASES

ENCLOSURES

BATTERIES

TRANS-  
FORMERS